

# YSHIELD® BVD | Shielding canopy | Double bed | VOILE

From fabric Voile with 38 dB attenuation at 1 GHz. Box-shape for double beds. Width: 220 cm, depth: 220 cm, height: 220 cm.




YSHIELD® BVD



YSHIELD® BVD



YSHIELD® Voile



YSHIELD GmbH & Co. KG  
 Rotthofer Straße 1  
 94099 Ruhstorf, Germany  
 Further information:  
[www.yshield.com](http://www.yshield.com),  
[info@yshield.com](mailto:info@yshield.com)

## Properties

Available fabrics:	Available shapes:
<p><b>Silver-Tulle:</b> High-end fabric with the <u>highest shielding attenuation</u>. High light transmission and air permeability, mechanically stable, free of crinkles. 48 dB shielding attenuation. <u>Groundable</u> with grounding plate hook-and-loop GV.</p>	<p><b>Pyramid single bed:</b> For a fast installation or a heavy roof pitch, suitable for single beds with a width of 100 cm. <u>Dimensions</u> (+/- 5% tolerance): Hem size at the bottom 1150 cm, height 240 cm. <u>Entrance:</u> Overlapping opening. Installation: Suspension with an inside ring at one point at the ceiling. <u>Scope of delivery:</u> Canopy, mounting material, 100 cm ring.</p>
<p><b>Voile:</b> By Swiss Shield®, <u>versatile characteristics</u> with a high shielding attenuation. High light transmission and air permeability, mechanically stable, free of crinkles. 36 dB shielding attenuation, not groundable.</p>	<p><b>Box single bed:</b> Spacious sense of space for single beds up to 120 cm width. <u>Dimensions</u> (+/- 5% tolerance): Width 120 cm, depth 220 cm, height 220 cm. <u>Entrance:</u> Overlapping opening. Installation: Suspension at four points at the ceiling. To stabilize the box shape, you can insert poles (not included in the delivery) into the tunnel, sewn at the top of the canopy. <u>Scope of delivery:</u> Canopy, mounting material.</p>
<p><b>Naturell:</b> By Swiss Shield®, made of <u>ecological cotton</u> with high shielding attenuation. Light transmission and air permeability are still acceptable, the fabric crinkles a lot. Shielding attenuation 38 dB. Not groundable.</p>	<p><b>Box double bed:</b> Spacious sense of space for single beds up to 220 cm width. <u>Dimensions</u> (+/- 5% tolerance): Width 220 cm, depth 220 cm, height 220 cm. <u>Entrance:</u> Two overlapping openings. Installation: Suspension at four points at the ceiling. To stabilize the box shape, you can insert poles (not included in the delivery) into the tunnel, sewn at the top of the canopy. <u>Scope of delivery:</u> Canopy, mounting material.</p>
<p><b>Other fabrics:</b> We will be happy to sew your canopy with another fabric. Just ask us for an offer.</p>	<p><b>Other shapes/dimensions:</b> We will be happy to sew your canopy with your required dimensions. Just ask us for an offer.</p>

## Swiss Shield® Shielding fabrics

This fabric is manufactured by Swiss Shield® in Switzerland with a patented, **invisible high-tech yarn**. At YSHIELD we value the constantly high quality of the fabrics - it's not for nothing that we are the world's largest Swiss Shield® distributor.

## Care instructions

- Gentle cycle at 30°C exclusively with our **TEXCARE** detergents
- Iron without steam at degree 1
- Drying at low temperature
- No bleaching
- No chemical dry-cleaning

## Grounding

This product with an electrically isolated surface **cannot be contacted or grounded**.

## Shielding attenuation HF & LF

This product **shields high frequency electromagnetic fields (HF)**. Unless otherwise stated, the indicated dB-values apply to 1 GHz. Measurement from 600 MHz to 40 GHz according to standards ASTM D4935-10 or IEEE Std 299-2006.

This product contains electrically conductive parts on the inside which can neither be contacted nor grounded. That's why individual areas **do not shield low frequency electrical fields (LF)**. In case this product is used as a Faraday cage (complete shielding on six sides), there will be no low frequency electrical fields (LF) on the inside, which can be proven with a potential free measurement.

## Laboratory & expert report of shielding attenuation up to 40 GHz

We have already invested in our **own professional EMV laboratory** years ago. We not only use it to create our laboratory screening reports but also to check each batch daily. Additionally, we have all our products checked by an **independent, well-respected expert**. Double checked for twice the safety. **Please find the reports above at the downloads.**